

## VENZ V10 comes with multiple connection options



\*HDMI 2.0 out (HDMI cable supplied in packaging)

\*USB x 3 ports

\*LAN RJ45 port 10/100Mbps

\*AV output port

\*Optical port

\*TF/MicroSD cardreader

VENZ V10 is powered by Amlogic S905 chip Quad Core 64bit A53 2.0GHz processor



VENZ V10 comes with our unique VENZ Android 6.0 software GUI with its modern look and ultra-fast functionality



android  
Lollipop 5.1



NETFLIX



VENZ V10 comes with support for 4K Ultra HD content up to 60fps 10-bit



Retail packaging content



IR Remote Control function scheme

 <ul style="list-style-type: none"> <li> -Power on and off</li> <li> -Mute</li> <li> -Clear cache kill all current process</li> <li> -Zoom out image</li> <li> -Zoom in image</li> <li> -Switch system launcher Home Menu</li> <li> -Page down</li> <li> -Page up</li> <li> -Page right</li> <li> -Page left</li> <li> -Switch video output resolution</li> <li> -Switch TV screen scale 16:9, 4:3</li> <li> -Select audio track</li> <li> -Select video subtitle</li> <li> -Quick open KODI music</li> <li> -Quick open KODI movie</li> <li> -Quick open KODI TV shows</li> <li> -Quick open KODI picture</li> <li> -Quick return home menu</li> <li> -Open system setting menu</li> <li> -Open current function menu</li> </ul>	 <ul style="list-style-type: none"> <li> -Right key/KODI play forward</li> <li> -Left key/KODI play backward</li> <li> -Up Key/KODI move up</li> <li> -Down Key/KODI move down</li> <li> -OK Key, enter current menu</li> <li> -Return to previous menu</li> <li> -Increase the volume</li> <li> -Decrease the volume</li> <li> -Play and Pause</li> <li> -Play Stop/Stop invalid KODI add-on</li> <li> -Play Previous item</li> <li> -Play Next item</li> <li> -Number input key</li> <li> -Switch to Mouse mode</li> <li> -Backspace error input</li> </ul>
--	--

## Specifications

<b>Chipset</b>	Amlogic S905
<b>Processor</b>	Quad Core ARM 64-bit Cortex A53 up to 2.0GHz
<b>GPU</b>	Penta Core Mali-450 up to 750MHz, 3D Graphics acceleration
<b>Memory</b>	1GB DDR3
<b>Internal storage</b>	8GB eMMC Flash
<b>Wireless connectivity</b>	2.4GHz 802.11 b/g/n WIFI
<b>Video Output</b>	HDMI 2.0 port up to UHD 4K @ 60fps
<b>Audio Output</b>	HDMI 2.0, AV out, Optical out
<b>Power Supply (adapter)</b>	AC-DC SPS adapter 5V/2A (FCC, CE, CCC certified)
<b>High Definition video output</b>	720P, 1080I, 1080P FHD, 3D Mode, UHD 4K @ 60fps 10-bit
<b>Support decoder format</b>	HD MPEG1/2/4,H.265/HEVC, H.264 , HD AVC/VC-1,RM/RMVB,Xvid/DivX3/4/5/6 ,RealVideo8/9/10
<b>Video formats</b>	MKV, WMV, MPG, MPEG, DAT, AVI, MOV, ISO, MP4, RM, DivX HD
<b>Music formats</b>	MP3, AAC, WMA, RM, FLAC, Ogg and programmable with 5.1 down-mixing
<b>Picture formats</b>	JPG, MJPEG, JPEG, BMP, PNG,TIFF, GIF
<b>Subtitle formats</b>	sub, smi, ssa, srt, idx + sub
<b>Network functionality</b>	PPPoE, VPN, Portable Wifi hotspot, Samba share, DLNA
<b>Supported file systems</b>	EXT3, FAT32, NTFS
<b>USB 2.0 Host</b>	USB HOST * 3
<b>Network</b>	RJ45 Cable socket support LAN speed to 10/100Mbps
<b>Operation System</b>	Android 6.0
<b>KODI</b>	Krypton 17