

Acer Extensa M2710\_E(DT.X0TEK.009)

Acer Extensa M2710\_E - MT - 1 x Core i5 6400 / 2.7 GHz - RAM 4 GB - HDD 1 TB - DVD-Writer - HD Graphics 530 - GigE - Win 10 Pro 64-bit - monitor:none



Acer Extensa EM2 series is built around companies'demands for reliable,easy to manage,expandable and thoroughly secure machines with a cost-effective design.

## Key Selling Points

Essential productivity  
Easy manageability and security  
Energy efficiency

## Product Features

### Essential productivity

Presenting dual monitor support,Extensa EM2 series doubles available viewing space and makes it easier to work with multiple applications and documents at the same time.

### Easy manageability and security

Valuable utilities conceived to simplify manageability and enhance security help companies to protect their assets from unauthorized access or data losses.

### Energy efficiency

All components within these desktops are free of hazardous substances,so they have a smaller footprint while helping to drive business success.

## Main Specifications

Product Description	Acer Extensa M2710_E - MT - Core i5 6400 2.7 GHz - 4 GB - 1 TB
Type	Personal computer - mini tower
Localisation	United Kingdom
Processor	1 x Intel Core i5 (6th Gen) 6400 / 2.7 GHz (3.3 GHz) (Quad-Core)
Processor Socket	LGA1151 Socket
Processor Main Features	Intel Turbo Boost Technology 2
Cache Memory	6 MB
Cache Per Processor	6 MB
RAM	4 GB (installed) / 16 GB (max) - DDR4 SDRAM
Storage Controller	SATA
Hard Drive	1 x 1 TB - SATA 6Gb/s - 7200 rpm
Optical Storage	DVD-Writer
Graphics Controller	Intel HD Graphics 530
Networking	GigE
Power	AC 120/230 V
OS Provided	Windows 10 Pro 64-bit Edition
Dimensions (WxDxH)	17.5 cm x 37.2 cm x 36.5 cm
Weight	6 kg

## Extended Specification

## General

Type	Personal computer
Product Form Factor	Mini tower
Embedded Security	Trusted Platform Module (TPM 2.0) Security Chip
Localisation	United Kingdom

## Processor / Chipset

CPU	Intel Core i5 (6th Gen) 6400 / 2.7 GHz
Max Turbo Speed	3.3 GHz
Number of Cores	Quad-Core
CPU Qty	1
Max CPU Qty	1
Processor Main Features	Intel Turbo Boost Technology 2
CPU Socket	LGA1151 Socket
Chipset Type	Intel H110 Express

## Cache Memory

Installed Size	6 MB
Cache Per Processor	6 MB

## RAM

Installed Size	4 GB / 16 GB (max)
Technology	DDR4 SDRAM
Effective Memory Speed	2133 MHz
Rated Memory Speed	2400 MHz
Form Factor	DIMM 288-pin
Features	Unbuffered
Configuration Features	1 x 4 GB

## Hard Drive

Type	HDD
Capacity	1 x 1 TB
Interface Type	SATA 6Gb/s
Spindle Speed	7200 rpm

## Storage Controller

Type	1 x SATA
------	----------

## Optical Storage

Type	DVD-Writer - SATA
------	-------------------

## Monitor

Monitor Type	None.
--------------	-------

## Graphics Controller

Graphics Processor	Intel HD Graphics 530
Video Interfaces	VGA, DVI

## Input Device

Type	Mouse, keyboard
------	-----------------

## Keyboard

Interface	USB
-----------	-----

## Mouse

Interface	USB
-----------	-----

## Networking

Ethernet Controller	Realtek RTL8111E
Data Link Protocol	Ethernet, Fast Ethernet, Gigabit Ethernet

## Expansion / Connectivity

Bays	5.25" 3.5"
------	---------------

Slots	DIMM 288-pin 1 (total) / 0 (free) x CPU 1 PCIe x16 1 PCIe x1 1 M.2 Card
-------	---

Interfaces	4 x USB 2.0 2 x USB 3.0 1 x audio line-out 1 x audio line-in 1 x LAN (Gigabit Ethernet) 1 x VGA 1 x DVI
------------	---

## Miscellaneous

Theft/Intrusion Protection	Security lock slot (cable lock sold separately)
Compliant Standards	BSMI, CB, FCC, RoHS, PC 2001, EuP

## Power

Device Type	Power supply
Nominal Voltage	AC 120/230 V
Power Provided	220 Watt
Efficiency	82%+
Power Factor Correction	Yes (active)

## Operating System / Software

OS Provided	Windows 10 Pro 64-bit Edition
-------------	-------------------------------

## Dimensions &Weight

Width	17.5 cm
Depth	37.2 cm
Height	36.5 cm
Weight	6 kg

## What's in the box

Acer Extensa M2710\_E  
Mouse,keyboard

Product data is provided by CNET,we do not warrant the accuracy and completeness of the material contained in this data sheet