

Acer Veriton X2640G_Ekbl(DT.VPUEK.001)

Acer Veriton X2640G_Ekbl - SFF - 1 x Core i3 7100 / 3.9 GHz - RAM 4 GB - HDD 1 TB - DVD-Writer - HD Graphics 630 - GigE - Win 10 Pro 64-bit - monitor:none



This affordable desktop offers excellent multitasking performance with essential manageability and security features in an energy-efficient design to meet your business needs.

Key Selling Points

Excellent multitasking performance
Vital security

Product Features

Form and function

This desktop delivers excellent multitasking performance to optimize your productivity. Easy expandability,affordable solutions,and other useful features efficiently handle your daily work needs.

Vital security

This desktop is simple to manage. TPM encryption protects files,passwords and vital data,so you can rest assured.

Main Specifications

Product Description	Acer Veriton X2640G_Ekbl - SFF - Core i3 7100 3.9 GHz - 4 GB - 1 TB
Type	Personal computer - small form factor
Localisation	United Kingdom
Processor	1 x Intel Core i3 (7th Gen) 7100 / 3.9 GHz (Dual-Core)
Processor Socket	LGA1151 Socket
Cache Memory	3 MB
Cache Per Processor	3 MB
RAM	4 GB (installed) / 16 GB (max) - DDR4 SDRAM
Storage Controller	SATA
Hard Drive	1 x 1 TB - SATA 6Gb/s - 7200 rpm
Optical Storage	DVD-Writer
Graphics Controller	Intel HD Graphics 630
Audio Output	5.1 channel surround
Networking	GigE
Power	AC 120/230 V
OS Provided	Windows 10 Pro 64-bit Edition
Dimensions (WxDxH)	10 cm x 35.4 cm x 26.5 cm
Weight	6 kg
Environmental Standards	ENERGY STAR Qualified

Extended Specification

General

Type	Personal computer
------	-------------------

Product Form Factor	Small form factor
Embedded Security	Trusted Platform Module (TPM 2.0) Security Chip
Localisation	United Kingdom

Processor / Chipset

CPU	Intel Core i3 (7th Gen) 7100 / 3.9 GHz
Number of Cores	Dual-Core
CPU Qty	1
Max CPU Qty	1
CPU Socket	LGA1151 Socket
Chipset Type	Intel H110 Express

Cache Memory

Installed Size	3 MB
Cache Per Processor	3 MB

RAM

Installed Size	4 GB / 16 GB (max)
Technology	DDR4 SDRAM
Effective Memory Speed	2400 MHz
Rated Memory Speed	2400 MHz
Form Factor	DIMM 288-pin
Features	Unbuffered
Configuration Features	1 x 4 GB

Hard Drive

Type	HDD
Capacity	1 x 1 TB
Interface Type	SATA 6Gb/s
Spindle Speed	7200 rpm

Storage Controller

Type	1 x SATA
------	----------

Optical Storage

Type	DVD-Writer - SATA
------	-------------------

Monitor

Monitor Type	None.
--------------	-------

Graphics Controller

Graphics Processor	Intel HD Graphics 630
Video Interfaces	VGA, DVI

Audio Output

Sound Output Mode	5.1 channel surround
-------------------	----------------------

Compliant Standards High Definition Audio

Input Device

Type Mouse, keyboard

Keyboard

Interface USB

Mouse

Interface USB

Networking

Data Link Protocol Ethernet, Fast Ethernet, Gigabit Ethernet

Expansion / Connectivity

Bays Internal 3.5"
External 5.25"

Slots 1 (total) / 0 (free) x CPU
DIMM 288-pin
1 PCIe x1
1 PCIe x16

Interfaces 4 x USB 2.0 (2 front, 2 rear)
4 x USB 3.0 (2 front, 2 rear)
1 x LAN (Gigabit Ethernet)
2 x microphone (1 in front)
2 x audio line-out/headphones (1 in front)
1 x audio line-in
1 x serial
1 x PS/2 keyboard
1 x PS/2 mouse
1 x DVI
1 x VGA

Miscellaneous

Compliant Standards VCCI, CB, FCC, RoHS, PC 2001, EuP

Power

Device Type Power supply

Nominal Voltage AC 120/230 V

Power Provided 220 Watt

Efficiency 82%+

Power Factor Correction Yes (active)

Operating System / Software

OS Provided Windows 10 Pro 64-bit Edition

Environmental Standards

ENERGY STAR Certified Yes

Dimensions &Weight

Width	10 cm
Depth	35.4 cm
Height	26.5 cm
Weight	6 kg

What's in the box

Acer Veriton X2640G_Ekbl
Mouse,keyboard

Product data is provided by CNET,we do not warrant the accuracy and completeness of the material contained in this data sheet