

Acer Veriton X2640G_Ekbl(DT.VPUEK.003)

SFF - 1 x Core i5 7400 / 2.7 GHz - RAM 4 GB - HDD 1 TB - DVD-Writer - HD Graphics 530 - GigE - Win 10 Pro 64-bit - monitor:none



This affordable desktop offers excellent multitasking performance with essential manageability and security features in an energy-efficient design to meet your business needs.

Key Selling Points

Excellent multitasking performance
Vital security

Product Features

Form and function

This desktop delivers excellent multitasking performance to optimize your productivity. Easy expandability,affordable solutions,and other useful features efficiently handle your daily work needs.

Vital security

This desktop is simple to manage. TPM encryption protects files,passwords and vital data,so you can rest assured.

Main Specifications

Product Description	Acer Veriton X2640G_Ekbl - SFF - Core i5 6400 2.7 GHz - 4 GB - 1 TB
Type	Personal computer - small form factor
Localisation	United Kingdom
Processor	1 x Intel Core i5 (6th Gen) 6400 / 2.7 GHz (3.3 GHz) (Quad-Core)
Processor Socket	LGA1151 Socket
Processor Main Features	Intel Turbo Boost Technology 2
Cache Memory	6 MB L3 Cache
Cache Per Processor	6 MB
RAM	4 GB (installed) / 16 GB (max) - DDR4 SDRAM
Storage Controller	SATA
Hard Drive	1 x 1 TB - SATA 6Gb/s - 7200 rpm
Optical Storage	DVD-Writer
Graphics Controller	Intel HD Graphics 530
Audio Output	5.1 channel surround
Networking	GigE
Power	AC 120/230 V
OS Provided	Windows 10 Pro 64-bit Edition
Dimensions (WxDxH)	10 cm x 35.4 cm x 26.5 cm
Weight	6 kg
Environmental Standards	ENERGY STAR Qualified

Extended Specification

General

Type	Personal computer
Product Form Factor	Small form factor
Embedded Security	Trusted Platform Module (TPM 2.0) Security Chip
Localisation	United Kingdom

Processor / Chipset

CPU	Intel Core i5 (6th Gen) 6400 / 2.7 GHz
Max Turbo Speed	3.3 GHz
Number of Cores	Quad-Core
CPU Qty	1
Max CPU Qty	1
Processor Main Features	Intel Turbo Boost Technology 2
CPU Socket	LGA1151 Socket
Chipset Type	Intel H110 Express

Cache Memory

Installed Size	L3 Cache - 6 MB
Cache Per Processor	6 MB

RAM

Installed Size	4 GB / 16 GB (max)
Technology	DDR4 SDRAM
Effective Memory Speed	2133 MHz
Rated Memory Speed	2400 MHz
Form Factor	DIMM 288-pin
Features	Unbuffered
Configuration Features	1 x 4 GB

Hard Drive

Type	HDD
Capacity	1 x 1 TB
Interface Type	SATA 6Gb/s
Spindle Speed	7200 rpm

Storage Controller

Type	1 x SATA
------	----------

Optical Storage

Type	DVD-Writer - SATA
------	-------------------

Monitor

Monitor Type	None.
--------------	-------

Graphics Controller

Graphics Processor	Intel HD Graphics 530
Video Interfaces	VGA, DVI

Audio Output

Sound Output Mode	5.1 channel surround
Compliant Standards	High Definition Audio

Input Device

Type	Mouse,keyboard
------	----------------

Keyboard

Interface	USB
-----------	-----

Mouse

Interface	USB
-----------	-----

Networking

Data Link Protocol	Ethernet,Fast Ethernet,Gigabit Ethernet
--------------------	---

Expansion / Connectivity

Bays	Internal 3.5" External 5.25"
------	---------------------------------

Slots	1 (total) / 0 (free) x CPU DIMM 288-pin 1 PCIe x1 1 PCIe x16
-------	---

Interfaces	4 x USB 2.0 (2 front,2 rear) 4 x USB 3.0 (2 front,2 rear) 1 x LAN (Gigabit Ethernet) 2 x microphone (1 in front) 2 x audio line-out/headphones (1 in front) 1 x audio line-in 1 x serial 1 x PS/2 keyboard 1 x PS/2 mouse 1 x DVI 1 x VGA
------------	---

Miscellaneous

Compliant Standards	VCCI,CB,FCC,RoHS,PC 2001,EuP
---------------------	------------------------------

Power

Device Type	Power supply
Nominal Voltage	AC 120/230 V
Power Provided	220 Watt
Efficiency	82%+
Power Factor Correction	Yes (active)

Operating System / Software

OS Provided	Windows 10 Pro 64-bit Edition
-------------	-------------------------------

Environmental Standards

ENERGY STAR Certified	Yes
-----------------------	-----

Dimensions &Weight

Width	10 cm
-------	-------

Depth	35.4 cm
-------	---------

Height	26.5 cm
--------	---------

Weight	6 kg
--------	------

What's in the box

Acer Veriton X2640G_Ekbl
Mouse,keyboard

Product data is provided by CNET,we do not warrant the accuracy and completeness of the material contained in this data sheet