


AV Cable Assembly



Dimensions : Millimetres

Notes:

1. Material

- 1.1 HDMI Cable: [(7/0.10TC×1P+7/0.10TC+FAM)×4+(7/0.10TC)×1P+(7/0.10TC)×3C]+AL+7/0.12 BC+128/0.12ALM+Black PVC Jacket.
OD: 6±0.2mm
Marking: E324703 AWM Style 20276 80°C 30V DVI Cable.

1.2 HDMI 19Pin Type A Male: Black Insulation, Gold Plated Contacts 3µ", Gold Plated Shell G/F.

1.3 DVI (24+1) Male: Black Insulation, Gold Plated Contacts G/F, Gold Plated Shell G/F.

1.4 Thumb Screw to be molded black PVC.


1.5 All Hood: Molded Black PVC.

2. Electrical

- 2.1 100% Open and Short Test.
- 2.2 Conductor Resistance: 5Ω Max.
- 2.3 Insulation Resistance: 10MΩ Min.
- 2.4 Hi-Pot: DC200V/0.01S.

3. Packaging: A PC/PE-Bag Packaging.

4. All Materials are RoHS Compliant.



Part Number Table

Description	Part Number
Audio / Video Cable Assembly, HDMI Type A Plug, DVI-D Dual Link Plug, 3 ft, 914mm, Black	PSG90342