

All Specifications (E2270SWDN)



E2270SWDN

This LED-backlit monitor delivers a solid performance for standard office and home applications. Coming in a classy black texturised finish, the tiltable widescreen model is equipped with a fast-reacting TN panel, boasting a 5 ms pixel response time for crisp, blur-free images. Intelligent programs such as Screen+ and i-Menu enhance the user experience and help to save energy. The eco-friendly Series 70 fulfils demanding

sustainability certificates such as Energy Star 6.0 and EPEAT Silver and is prepared for both VESA wall mount and Kensington security devices.
Discover all benefits of the series 70 monitors now!

Screen detail

Monitor Size	21.5 inch
Visible Screen size	476.64x268.11 mm
Screen Format	16:9
Brightness	200 cd/m ²
Contrast Ratio	700:1
Dynamic Contrast Ratio	20M:1
Viewing Angle	90/65 °
Response time	5 ms
Panel type	TN
Refresh rate	60Hz
Resolution	1920x1080 PX
Pixel pitch	0.248

Colors	16.7 Million
EAN	4038986125697
Warranty period	3 Years
Backlight	WLED
Bezel type	Normal

Connections

DVI	✓
VGA	✓

Audio

Speaker power	Watt
---------------	------

Whats in the box

VGA Cable	✓
DVI Cable	✓
Power shuko c7 Cable	✓

Power

100 - 240V 50/60Hz

Power Source

Internal

Power supply

Ergonomics

Swivel

0°

Tilt

-5/+15°

Pivot

/90°

Regulations

TUV GS



FCC



Gost



Rohs compliant



CE

