



Stellar Labs Part #24-15410, 24-15411, 24-15412, 24-15413, 24-15414, 24-15415, 24-15416, 24-15417, 24-15418, 24-15419

22 AWG (Solid) Tinned Copper Wire, UL Style UL 1007/ UL Style 1569, Hook Up Wire

Product Construction

22 AWG (Solid) Tinned Copper Wire



Conductor:

22 AWG (Solid) Tinned Copper Wire Conductor per ASTM B-33

Insulation:

Color coded PVC

Temperature: UL 1007, -40° to +80°C

Temperature: UL 1569, -40° to +105°C

Voltage Rating: 300 volts

Applications:

Dual Rated UL Style 1007 and UL Style 1569

Specifications

Gauge	22 AWG
Strands	(Solid) Tin Copper Wire
Nominal Insulation Wall	0.016 in.
Insulation Type	PVC
Nominal O.D.	0.057 in.
Insulation Temperature	-40°C to +80°C / -40°C to +105 °C
Voltage Rating	300 V

Other Information

Approvals	CSA TR-64 90°C RoHS Compliant UL 1007, UL 1569 VW-1
------------------	--