

Stellar Labs Part # 24-15450, 24-15452, 24-15456, 24-15459

26 AWG (Solid) Tinned Copper Wire UL Style 1007 and UL Style 1569 VW-1 80°C / 105°C 300 Volts CSA SR PVC FT1, Hook Up Wire

**Product Construction**

**Conductor:**

- 26 AWG (Solid) Tinned Copper Wire
- Solid Tinned Copper Wire Conductor per ASTM B-33

**Insulation:**

- UL 1007 color coded PVC
- Temperature: -40° to +80°C
- UL 1569 color coded PVC
- Temperature: -40°C to +105°C
- Voltage Rating: 300 volts

**Applications:**

- Solid Copper Wire UL Style 1007 / UL Style 1569 80°C / 105°C 300 Volt Hook-Up Wire
- Point to point wiring
- Internal wiring of meters, panels, electrical and electronic equipment

**Industry Approvals:**

- UL Style 1007
- UL Style 1569
- CSA-TR-64
- RoHS Compliant
- OSHA acceptable

**Packaging:**

- 1000 ft. spools
- 100 ft. spools
- Also available on bulk reels



**Specifications**

Gauge	26 AWG
Strands	(Solid) Tin Copper Wire
Nominal Insulation Wall	0.015 in.
Insulation Type	PVC
Nominal O.D.	0.048 in.
Insulation Temperature	UL Style 1007 -40 to +80 °C UL Style 1569 -40 to +105 °C
Voltage Rating	300 V

**Other Information**

Approvals	CSA TR-64 90°C RoHS Compliant UL 1007, UL 1569 VW-1
-----------	--