

148-90049

Article Number: 148-90049

Description: HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 3-Port, (PC), Orange, 400/pkg



Base Data	Local Order Number	HCPM-3
	Type	HCPM-3
	Color	Clear (CL) Orange (OG)
	Features and benefits	<ul style="list-style-type: none"> • Double-spring technology for safe, secure and reliable connections. • Smaller footprint fits in tight spaces. • Low insertion force makes installation of solid or stranded copper wire fast and easy. • Color coded for easy identification of size. • Each port accepts multiple wire diameters for flexible applications. • Accepts 12–22 AWG solid wire and 14–22 AWG stranded wire.
	Quantity Per	pack
	Brand Family	HelaCon
	Product Description	HelaCon Plus Mini Wire Connectors replace traditional twist-on wire connectors. They provide faster, easier and more reliable connection and distribution of cable and conductors in electrical installation applications. Mini connectors have a compact footprint and can be applied tool-free using convenient, push-in simplicity. Internal double-spring technology is approved for solid and stranded wires.
	GLOBAL PART NAME (auto set)	HCPM-3-PC-CL/OG
	Voltage Rating (cULus)	600 V
	Voltage Rating (VDE)	450 V
	Short Description	HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 3-Port, (PC), Orange, 400/pkg
	Product Dimensions	Length L (Imperial)
Length L (Metric)		16.5mm
Max Current		24A
Max Voltage		600V
Number of Conductors		3
Width W (Imperial)		0.59"
Width W (Metric)		15.1mm

148-90049

HellermannTyton

Product Dimensions	Height H (Imperial)	0.30"
	Height H (Metric)	7.70mm
	Depth D (imperial)	0.65"
	Depth D (metric)	16.5mm
Material and Specifications		
	Material	Polycarbonate (PC)
	Material Shortcut	PC
	Flammability	UL 94 V0
	Halogenfree	Yes
	Operating Temperature	-22°F to +185°F (-30°C to +85°C)
	ROHS Compliant	Yes
	UL Listed (US and Canada)	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	400
	Package Quantity (Metric)	400Pieces