

Industrial Probes with Terminal Head



- Strong 6m diameter stainless steel stem
- Waterproof aluminium terminal head
- **IP67** protection
- Suitable for connection to any PT100 instrument - 2, 3 or 4 wire

The head of the probe contains a terminal block allowing connection to the measuring instrument via a M20 gland.

Sensor PT100, 4 wire to **BS1904 (1984) Class B** and **DIN 43760** 100Ω @ 0°C

Temperature head Die cast aluminium, epoxy coated, Screwed lid with retaining chain
IP67 rated

Temperature range -50°C to +450°C

Mfr. List Nos. PT4 6 x 150 = 560-157, PT4 6 x 300-KNE = 560-169
PT4 6 x 400 = 708-8449

FOR SUITABLE COMPRESSION GLAND SEE **ORDER CODE 254-654**

SEN157

Probe Length **Order Code**

150mmmm [**560-157**

300mmmm [**560-169**

400mm **708-8449**