

EAO – Your Expert Partner for Human Machine Interfaces

10-2513.1149 - Single-LED

10-2513.1149 - Single-LED



Attention: The preview is based on a sample product. This can differ from your current configuration.

Other Attributes

Weight	0,002 kg
Operation current	5 mA \pm 15 %
Operating voltage	28 V AC/DC +10 %


Illumination

Socket	BA9s
LED colour	white

Optics

Lumi. intensity	750 mcd
Dom. wavelength	x0.31/y0.32 nm

Dimensions



Additional information

The max. overall length of the lamp may not exceed 25mm

Electrical and optical data are measured at 25 °C

The specified 12, 24, 28, 48 VAC/DC versions are built with a bridge rectifier

Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination