

**Model: X2C4000VMP/G**



**Xvision PRO-HD 4MP H265 Vandal IR Dome IP Camera, 20m IR, Motorised Auto Focus Lens, Video Analytics – White or Grey**

**Specifications:**

Brand	Xvision Pro-HD
Model Number	X2C4000VMP/G
Style	High Definition Varifocal Dome Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	Yes
Motorised Panning	No
Motorised Tilting	No
Digital Zoom	No
Audio	Yes
Mounting Type	Wall or Ceiling
Product Dimensions (WxHxD) in mm	151x108x151
Product Weight	0.70Kg
Shipping Dimensions (WxHxD) in mm	N/A

Shipping Weight	N/A
Warranty	1 Year Warranty (extendable to 3 years)
Image Sensor Type	1/2.9" Sony CMOS
Image Sensor Resolution	4 Mega Pixel
Minimum Illumination	0.0001 Lux (0 Lux IR On)
Night Vision	20m IR Night Vision
Other Features	Automatic White Balance Automatic Gain Control Automatic Electronic Iris DNR (Digital Noise Reduction) WDR (Wide Dynamic Range)
Lens	2.8-12.0mm Motorised Lens
Viewing Angle	23-98°
Video Compression	H.265/264
Video Streams	1024Kbps-6144Kbps
Stream Types	Complex Stream/Video Stream
Video Resolutions & Frame Rates	2592x1520 @ 20fps, 2048x1536 @ 25fps, 1920x1080 @ 25fps, 1280x720 @ 25fps
Network Connection	RJ45 Sockett (10/100 BASE-T)
Wi-Fi Support	No
Network Protocols Supported	TCP/IP, UDP, HTTP, DHCP, RTP/RTSP, DNS, DDNS, NTP, PPPoE, UPNP, SMTP
Browser Support	Internet Explorer
Mobile Phone Support	Android, iPhone
User Authentication	Yes
Simultaneuos Viewers	10
Power Over Ethernet	Yes
Operating Voltage	12V DC
Power Consumption	<5W
Easy Fit	Yes (Optional Ethernet Over Mains Adaptor)
Motion Detection	No

Presents	No
Guard Tours	No
Email Alerts	Yes
On Board Recording	Yes
Alarms	Yes
Multi Camera Software	Yes