




PO:AVS04 17	Cello Electronics (UK) Ltd.	
	Product Photo	
General Features	EAN	5060062267594
	Model No.	C85ANSMT 4K
	Panel(60Hz/120Hz/3D)	T850QVR01.1
	Destination Country	UK
	Safety and Regulation	CE
	Panel System	85 inch LED Panel(Approx. 215.9cm)
	Max. Resolution	3840 x 2160
	Contrast Ratio (Typical)	4000: 1
	Brightness(TYP cd/m2)	300
	Display Colors	1.07G
	Viewing Angle(L/R/U/D)	89/89/89/89(CR≥10)
	HD Supported Definitions	3840*2160/1080p/1080i/720P/576P/480P
	AC Switch	N/A
Cabinet Color	Piano Black	
Wall Mounting Support(Screw Size)	800 x 400mm / (M8 x 20)	
Reception	TV Solution	Mstar3458+Mstar9280
	TV System	DTV:DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML, MPEG 4
	TV Band	DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz)
	5V from Antenna	N/A
	Tuning System	FST
	Clock / Time Display	N/A
	Number of channel for storing	400 Digital
Sound	Bass	YES
	Treble	YES
	Balance	YES
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	2 x 8W
	Speaker Frequency range	150-20K Hz
	Speaker Distortion	<=7% Max
	Speaker Impedance	8ohm
Connector Jacks	RF Antenna	1
	HDMI	YES x 3 (ver2.0)
	CVBS	YES x 1
	PC In	N/A
	Audio In	CVBS Audio x1
	Scart	N/A
	YPbPr	N/A
	Digital Audio out	YES× 1
	Earphone Out	N/A
	USB on TV	YES× 1(Multi Media Movie: *.mpg, *.dat, *.vob, *.avi, *.ts, *.mov,*.mkv,*.mp4 Music: *.mp3, *.wma, *.m4a, *.aac Photo: *.jpg, *.bmp, *.png)
	CI	N/A
	RCA	YES× 1
	RJ45 on Android	YES× 1
	Micro SD card on Android	YES× 1
	USB on Android	YES× 2(Multi Media & Wireless Mouse and Keyboard)

PO:AVS04 17	Cello Electronics (UK) Ltd.	
	Product Photo	
Android	SOC	M509280 PBM, ARM Cortex A7 quad core CPU
	RAM	1GB DDR3
	GPU	6 core ARM Mali-450MP4
	Built-in Flash	4GB
	Wi-Fi	YES× 1
	OS	Android 4.4.4
Other Features	APS	DVBT, DVBC storage in capture order
	OSD Language	English, Deutsch, Francais, Espanol, Portugese, Italian.
	EPG (Electronic Program Guide)	7 days
	Automatic Tuning	YES
	Sleep Timer	YES(240min)
	Color Temperature Adjustment	YES
	Picture Mode	Standard / Dynamic / Mild / User
	Home Mode	YES
	Wifi on Android	YES
	Hotel Mode	YES
Power	Power Supply	AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	250W
	KWh/annum	365kWh
	Max power Consumption	350W
	Standby Power Consumption	<0.5W
	Energy Efficiency Class	A
Accessories	USER'S Manual	N/A
	Remote Control	YES x 1
	Power Cable	YES x 1
	Adapter	N/A
	Adapter Cables	N/A
	Warranty	YES x 1
	Battery	1.5V(AAA)×2
Dimension	Unit Dimension With Stand (W x D x H mm)	1936 x 328 x 1180mm
	Unit Dimension Without Stand (W x D x H mm)	1936 x 93 x 1116mm
	Weight of unit(kg)	56

ATTN: the panels parameters listed in the spec are only for reference .