



msi


GRAPHICS CARD GEFORCE® GTX 1050 Ti AERO ITX 4G OCV1



SPECIFICATIONS

Model Name	GeForce® GTX 1050 Ti AERO ITX 4G OCV1
Graphics Processing Unit	NVIDIA® GeForce® GTX 1050 Ti
Interface	PCI Express 3.0 x16
Core Name	GP107-400
Cores	768 Units
Core Clocks	1455 MHz / 1341 MHz
Memory Clock Speed	7008 MHz
Memory	4GB GDDR5
Memory Bus	128-bit
Output	DisplayPort / HDMI / DL-DVI-D
HDCP Support	2.2
Power consumption	75 W
Recommended PSU	300 W
Card Dimension(mm)	170 x 111 x 39 mm
Weight (Card / Package)	317 g / 717 g
Afterburner OC	Y
DirectX Version Support	12
OpenGL Version Support	4.5
Maximum Displays	3
G-SYNC™ technology	Y
Adaptive Vertical Sync	Y

CONNECTIONS



FEATURES



SMALL FORM FACTOR

MSI AERO ITX cards offer the power of a full size graphics card in an incredibly small package.



PERFECT IN ANY CASE

Thanks to a small form factor, MSI AERO ITX cards will fit into virtually any case.



TORX FAN

This Award-winning Fan design combines two different fin designs for cool & quiet gaming.



OC PERFORMANCE

MSI OC graphics cards are equipped with higher clock speeds out of the box for increased performance.



Military Class 4 Components

Using only the highest quality components means you get reliable and stable in-game performance.



MSI Afterburner

The ultimate overclocking software with advanced control options and real-time hardware monitor.



NVIDIA G-SYNC™

Gives you more of what you want in a gaming experience. Incredibly smooth, tear-free gameplay at refresh rates up to 240 Hz.



PASCAL PERFORMANCE

Pascal-powered graphics cards give you superior performance and power efficiency to deliver the best gaming experiences.