



WRAPTOR Series Self-Laminating Vinyl Wire and Cable Labels

Part Number:

WRAP-4-427

Label/Tape Size:

1.5 in H x 1 in W

Material:

Vinyl

Material Number:

B-427

Color:

Clear/White

For Use with Printer:

WRAPTOR™ Wire Marking System



OVERVIEW

Self-Laminating Vinyl (B-427) is an excellent material for wire and cable identification. This material has good clarity, conformability and is self-extinguishing.

- Provided in a self-laminated format with a white printable zone and translucent overlaminating area to protect text
- Durable, permanent acrylic adhesive has outstanding water and oil resistance
- RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC; UL approved
- Service temperature of -40°F to 158°F (-40°C to 70°C)

Anti-Skid Surface?	N/A
Material Number	B-427
Dimensions	1.5 in H x 1 in W
UOM	Roll of 3600 Labels
Finish	Matte
Indoor or Outdoor Use	Outdoor Use
Label/Tape Size	1.5 in H x 1 in W
Maximum Service Temperature °F	140 °F
Maximum Wire Diameter	0.32 in
Maximum Wire Gauge	6 gauge
Minimum Service Temperature °F	-40 °F
Minimum Wire Diameter	0.16 in
Minimum Wire Gauge	14 gauge
Overlaminated Included	Overlaminated Included
Pre-Printed Areas on Label	Colored Write-On Area
Printable Area Dimensions	0.5 in H x 1 in W
Printable Area Height	0.5 in
Printable Area Width	1 in
Product Number	61386
UPC	662820613862
Quantity per Roll	3600
Quantity per Row	1
Tamper Indication Type	N/A
Thickness	0.004 in
Trade Name	Wraptor™
Adhesive Type	Acrylic
Applications	Cable & Wire Marking, Panel Labeling
Color	Clear/White
For Use with Printer	WRAPTOR™ Wire Marking System
Header	No Header

Label/Media Format	Roll
Material	Vinyl
Material Properties	Flame-retardant, Self-Laminating
Print Technology	Thermal Transfer
Resistance Properties	Chemical-Resistant, Humidity-Resistant, Oil-Resistant, Water-Resistant, Weather-Resistant
Shape	Rectangle
Suggested Ribbon Series	R4300