

151-01565

Article Number: 151-01565

Description: Wedge Clip, 0.0"-.20" Panel Thickness, PA66HSGF, Black/Green, 200/bag



Base Data	
Local Order Number	151-01565
Type	BCAA
Color	Green (GN) Black (BK)
Features and benefits	<ul style="list-style-type: none"> • Two-piece ratcheting wedge design allows for easy, positive-locking size adjustment. • Peel and stick 3M™ VHB™ adhesive inside clip increases grip and enables one-hand installation. • Heat-stabilized, glass-filled PA66 assembly delivers remarkable extraction force without drilling. • Three sizes cover a wide range of mounting thicknesses, reducing part inventory. • 4-way, wide slot accommodates our heavy-duty and Wide-Strap Series Cable Ties.
Quantity Per	bag
Product Description	The Wedge Clip, paired with any HellermannTyton heavy duty Cable Tie, routes cables along a frame or rail in vertical or horizontal applications. A robust design and durable materials make it ideal for extreme-duty applications. The integrated wedge mechanism slides along a stepped grade until snug against the mounting surface. Inside the clip is a 3M™ VHB™ (Very High Bond) adhesive pad, which actually builds strength over time. This holds the clip to the work surface instantly, enabling installers to place it into position without worrying about it falling off prior to fastening. The combination of adhesive and the clip's vice-like compression result in incredible extraction force without the need to drill holes. The Wedge Clip is offered in three sizes.
GLOBAL PART NAME (auto set)	BCAA-PA66HSGF30-BK/GN
Short Description	Wedge Clip, 0.0"-.20" Panel Thickness, PA66HSGF, Black/Green, 200/bag
Product Dimensions	
Length L (Imperial)	1.21"
Length L (Metric)	30.8mm
Length L2 (Metric)	27.0mm
Width W (Imperial)	1.13"
Width W (Metric)	28.6mm
Height H (Imperial)	1.70"
Height H (Metric)	43.10mm
Height H2 (Metric)	12.5mm

151-01565



Product Dimensions	Panel Thickness Max. (Imperial)	0.20"
	Panel Thickness Max. (Metric)	5.0mm
	Panel Thickness Min. (Imperial)	0.00"
Material and Specifications		
	Material	Polyamide 6.6, heat stabilized, glass fiber reinforced (PA66HSGF30%)
	Material Shortcut	PA66HSGF30
	Adhesive	Acrylic foam
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +284°F (-40°C to +140°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	200
	Package Quantity (Metric)	200
	Weight (Metric)	4.39985kg
	Weight (imperial)	9.7lbs