

GCS632U

## MiniView™ Micro USB PLUS KVM Switch with audio and cables



### 2-Port USB VGA Cable KVM Switch with Audio

Introducing IOGEAR's 2-Port MiniView™ Micro USB PLUS KVM switch – the simplest way to simultaneously control and switch between two computers from with a single USB keyboard, monitor and USB mouse. This self-powered KVM switch features the unique USB mouse and keyboard emulation to ensure smooth operation, as well as support for Plug-n-Play monitors and most wheel mice. With 6' long KVM cables molded into the MiniView Micro USB PLUS, all you need to do is to plug it into your computers and you've got a complete KVM solution from IOGEAR.

### Video and Audio Support

Our patented VSE Video Signal Enhancement® technology provides rich, 32-bit color at resolutions up to 2048 x 1536. Another big plus is this 2-Port VGA KVM's capability to provide audio support, allowing you to share your multimedia speakers among the two connected computers.

- Use one USB keyboard, monitor and USB mouse to control two USB computers
- Increase security for your intranet by separating a PC connected to the Internet and a PC connected to an Intranet
- 6' long molded-in cables to simplify setup
- Share your multimedia speakers among the two connected computers
- Full support for Mac and Sun systems
- Supports special keys on Mac and Sun keyboards
- Port selection through convenient Hot Keys
- USB sniffing technology allows complete USB mouse and keyboard emulation for error-free boot-up
- Plug-n-Play monitor support
- Support video resolutions up to 2048 x 1536
- No software required
- Built in AutoScan mode
- LEDs allow for easy status monitoring
- 3 Year Limited Warranty



## Requirements

### Console:

- 1 x VGA display
- 1 x standard 104 key wired USB keyboard
- 1 x standard 2 or 3 button wired USB mouse

### Computers:

- 1 x VGA port
- 1 x USB ports
- 1 x 3.5mm audio port

### Operating Systems:

- Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10
- Mac OS 9 to 10.x
- Oracle® Solaris
- Linux®, Unix and other USB supported systems\*

\*Additional drivers and support may be needed

\*\*IOGEAR's DynaSync provides the EDID support for Windows(R) 7

## Package Contents

- 1 MiniView Micro USB PLUS 2 Port KVM Switch
- 1 User Manual
- 1 Quick Start Guide
- 1 Warranty Registration Card

## Specifications

Function	GCS632U	Dimensions	GCS632U
<b>CPU Connectors</b>		<b>POP Information</b>	
Monitor	2 x HDB15 Male	10" Peg Hook	4
Audio	2 x stereo speaker	<b>Unit Dimensions</b>	
Keyboard & Mouse	2 x USB Type A	Width	3.06 in. (7.8 cm.)
<b>Console Connectors</b>		Height	1.00 in. (2.5 cm)
Mouse	1 x USB Type A	Depth	2.25 in. (5.7 cm)
Keyboard	1 x USB Type A	<b>Inner Pack</b>	
Monitor	1 x HDB15 Female	Width	6.44 in. (16.4 cm)
Audio	1 x stereo speaker	Height	9.19 in. (23.3 cm)
<b>Cable Length</b>	6 ft. (1.83 m.)	Length	7.00 in. (17.8 cm)
<b>Cable Connections</b>		Inner Pack Qty.	3
Input	USB	<b>Unit Package Dimensions</b>	
Output	USB	Width	6.25 in. (15.9 cm.)
<b>CPU or KVM Connection</b>	USB	Height	8.81 in. (22.4 cm.)
		Depth	2.25 in. (5.7 cm.)
		<b>Master Carton</b>	
		Width	13.38 in. (34.0 cm)
		Height	10.13 in. (25.7 cm)
		Depth	14.75 in. (37.5 cm)
		Master Carton Qty.	12
		<b>Weight</b>	
		Master Carton Wt.	15.05 lbs. (6.83 kg)
		Inner Pack Wt.	3.4 lbs (1.54 kg)
		Unit Pack Wt.	1.05 lbs. (0.48 kg)
		Unit Wt.	0.80 Lbs. (0.36 kg.)