

ATT-224H/WS - PA Attenuator



Wall-Mounted PA Volume Controls

- Recessed control to prevent unintentional readjustment
- Attenuation in 11 steps and OFF
- Audio transformer for 100 V line technique
- White plastic front panel (removable) and knob
- Flush mounting in standard wall boxes
- Surface mounting with matching housing ATT-200, available at option

Technical Data

Frequency range	: 50-18,000 Hz
Power rating	: 24 W
Priority facility	: no
Dimensions	: 85 x 85 x 45 mm
Mounting depth	: 37 mm
Weight	: 160 g
Surface-mounted housing	: ATT-200