

ATT-235H/WS - PA Attenuator



Wall-Mounted PA Volume Controls

- Recessed control to prevent unintentional readjustment
- Attenuation in 11 steps and OFF
- Audio transformer for 100 V line technique
- White plastic front panel (removable) and knob
- Flush mounting in standard wall boxes
- Surface mounting with matching housing ATT-200, available at option

Technical Data

| | |
|-------------------------|-------------------|
| Frequency range | : 50-18,000 Hz |
| Power rating | : 35 W |
| Priority facility | : no |
| Dimensions | : 85 x 85 x 45 mm |
| Mounting depth | : 34 mm |
| Weight | : 220 g |
| Surface-mounted housing | : ATT-200 |