

PA-160 - PA Mixing Amplifier



Mono PA mixing amplifier

- 1 x 60 W
- Silent operation due to fanless cooling concept
- 3 inputs via comb. jacks XLR/6.3 mm jack (mic/line)
- Continuously adjustable input sensitivities
- Input 1 and 2 with selectable priorities
- Speaker outputs via screw terminals
- Connection for external mute switch
- Phantom power, can be switched for each input
- 2-way tone control for the output
- LED indication for level, clip and protect
- Recessed operating controls on the front panel to prevent unintentional readjustment
- 482 mm (19") rack installation with supplied mounting brackets
- Mains operation or 24 V emergency power operation

Technical Data

Channels	: 3
Zones	: -
Power rating	: 60 W
Power rating at 2 Ohm	: -
Power rating at 4 Ohm	: 1 x 60 W
Power rating at 8 Ohm	: -
Power rating at 100 V	: 1 x 60 W
Power rating with 4 Ohm bridged operation	: -
Power rating with 8 Ohm bridged operation	: -
Peak music power output (P _{MAX})	: -
Output impedance	: -
Inputs	: 1.5-320 mV
Attenuation factor	: -
Frequency range	: 80-16,000 Hz
Crossover network	: -
Crossover frequency	: -
Integrated limiter	: -
Equalizer bass	: ± 12 dB/100 Hz
Equalizer midrange	: -
Equalizer treble	: ± 12 dB/10 kHz
S/N ratio	: > 66 dB
Crosstalk attenuation	: -
THD	: < 0.1%
Power supply	: ~ 230 V/50 Hz/120 VA, DC current 24 V/3 A
Mains voltage	: ~ 230 V
Mains frequency	: 50 Hz
Power consumption, operation	: 120 VA
Power consumption, standby	: -
Standby current	: -
Operating voltage (possible alternative)	: DC current 24 V
Power supply (possible alternative)	: DC current 3 A
Admiss. ambient temp.	: 0-40 °C
Dimensions	: 430 x 88 x 225 mm, 2 RS

Width
Height

: 430 mm
: 88 mm



CPC
FULWOOD
PR29PP
03447 880088



CPC
FULWOOD
PR29PP
03447 880088

Depth	: 225 mm
Rack spaces, RS	: 2
Weight	: 4.26 kg
Connections	: 3 x XLR/6.3 mm jack (mic/line) screw terminals (speakers)