


SA-130DMP - Amplifier




Stereo amplifier, 140 W with integrated MP3 player, Bluetooth receiver, FM radio, USB interface and SD/MMC card slot.

- Bluetooth receiver for wireless connection of laptops, smartphones or tablet PCs
- USB storage media can be connected directly
- For SD/MMC cards up to 32 GB (FAT16/FAT32), available at option
- Adjustable microphone input and aux input on the front panel
- Adjustable stereo line input
- Insert facility, e.g. for effect units, equalizers, feedback controllers
- 2-way tone control
- Adjustable master output
- 482 mm (19") rack installation, 1 RS

Technical Data

Channels	: 2
Zones	: -
Power rating	: 140 W
Power rating at 2 Ohm	: -
Power rating at 4 Ohm	: 2 x 70 W
Power rating at 8 Ohm	: -
Power rating at 100 V	: -
Power rating with 4 Ohm bridged operation	: -
Power rating with 8 Ohm bridged operation	: -
Peak music power output (P_{MAX})	: -
Output impedance	:
Inputs	: 480 mV/20 k Ohm (line) 1.3 mV/500 Ohm (mic) 190 mV/10 k Ohm (aux) 580 mV/22 k Ohm (amp in)
Attenuation factor	:
Frequency range	: 20-20,000 Hz
Crossover network	: -
Crossover frequency	: -
Integrated limiter	: -
Equalizer bass	: ± 12 dB/100 Hz
Equalizer midrange	: -
Equalizer treble	: ± 10 dB/10 kHz
S/N ratio	: 90 dB
Crosstalk attenuation	: -
THD	: 0.1%
Power supply	: ~ 230 V/50 Hz/350 VA
Mains voltage	: ~ 230 V
Mains frequency	: 50 Hz
Power consumption, operation	: 350 VA
Power consumption, standby	: -
Standby current	: -
Operating voltage (possible alternative)	: -
Power supply (possible alternative)	: -

Admiss. ambient temp.
Dimensions
Width
Height



MONACOR®

: 0-40 °C
: 482 x 44 x 245 mm
: 482 mm
: 44 mm

CPC
FULWOOD
PR29PP
03447 880088



CPC
FULWOOD
PR29PP
03447 880088

Depth	: 245 mm
Rack spaces, RS	: 1
Weight	: 4.9 kg
Connections	: 1 x RCA L/R (line), 1 x XLR/6.3 mm jack (mic), 1 x 3.5 mm jack (aux), 1 x RCA L/R (amp in), 1 x RCA L/R (amp out), screw terminals (speakers)