

LG 27MP38VQ-B 68.6 cm (27") LED LCD Monitor - 16:9 - 5 ms - 1920 x 1080 - Full HD - HDMI - VGA

by **Lg Electronics**

Using the right computer monitor might be the difference between a good presentation and a great presentation. LG offers dozens of innovative options to help you make the right impression, including 3D monitors that bring two-dimensional images to startling reality, IPS monitors with wide viewing angles and virtually no color shift, slim LED monitors, and ultra widescreen monitors that can be split into up to four windows for the ultimate in multitasking. Explore our full range of LG computer monitors, as well as our newest computer accessories, and create a space that's as functional as it is stylish.

>

This item is packaged with:

Specifications are provided by the manufacturer. Refer to the manufacturer for additional explanations.

Extended Specifications

Product Details and specifications are provided by manufacturer

Basic

Aspect Ratio:	16:9
Backlight Technology:	LED
Brand Name:	LG
HDMI:	Yes
Maximum Resolution:	1920 x 1080
Number of Screens:	1
Product Type:	LCD Monitor
Response Time:	5 ms
Screen Mode:	Full HD
Screen Size:	68.6 cm (27")
VGA:	Yes

General Information

Brand Name:	LG
Manufacturer Part Number:	27MP38VQ-B
Manufacturer Website Address:	http://www.lge.co.uk
Manufacturer:	LG Electronics
Packaged Quantity:	1
Product Model:	27MP38VQ-B
Product Name:	27MP38VQ-B Widescreen LCD Monitor
Product Type:	LCD Monitor

Interfaces/Ports

HDMI:	Yes
VGA:	Yes

Technical Information

Aspect Ratio:	16:9
Backlight Technology:	LED
Number of Screens:	1
Response Time:	5 ms
Screen Mode:	Full HD
Screen Size:	68.6 cm (27")

Video

Maximum Resolution:	1920 x 1080
---------------------	-------------

Printed on: 11/12/2017 at 2:4:56

Prices and other details current at the time and date page was printed (subject to change).