



LG 24MP59G-P 61 cm (24") LED LCD Monitor - 16:9 - 5 ms - 1920 x 1080 - 16.7 Million Colours - 250 cd/m² - 5,000,000:1 - Full HD - HDMI - VGA - DisplayPort - 17.10 W - Black

by *Lg Electronics*

Full HD Gaming with 1ms Motion Blur Reduction The Full HD display with 1ms Motion Blur Reduction allows gamers to enjoy the precision and accuracy needed to play at a very high level. With a response time that is virtually 1ms, blurring and ghosting are reduced to make the action smoother and gaming more precise.

AMD FreeSync™ FreeSync™ reduces the tearing and stuttering that occur between a graphic card's frame rate and a monitor's refresh rate. With FreeSync, gamers can experience seamless, fluid movement throughout their games.

Dynamic Action Sync Gamers can experience optimized, fast-paced gaming with Dynamic Action Sync. Dynamic Action Sync is a feature that minimizes input lag so the game play in RTS games is more responsive.

Black Stabilizer Keep visibility even in dark scenes. LG's Black Stabilizer senses dark scenes and helps make it brighter so that you can find the enemies hiding and waiting to attack your player in the dark.

Game Mode Set your game mode to optimize and customize your gaming conditions. There are 3 gamer modes, 2 First-Person-Shooter modes and even a RTS pre-set mode so you can choose the best mode for you and the game you're playing.

V-Line Stand The sleek design of this gaming monitor is accentuated by red color accents on the V-shape stand. This monitor will feel right at home as part of any gamer's desktop setup.

>

This item is packaged with:

Specifications are provided by the manufacturer. Refer to the manufacturer for additional explanations.

Extended Specifications

Product Details and specifications are provided by manufacturer

Additional Product Specifications

Full Product Specifications: [Click to view](#)

Basic	
Aspect Ratio:	16:9
Backlight Technology:	LED
Brand Name:	LG
Brightness:	250 cd/m ²
Colour Support:	16.7 Million Colours
Colour:	Black
Contrast Ratio:	5,000,000:1
DisplayPort:	Yes
Energy Star:	Yes
HDMI:	Yes
Maximum Resolution:	1920 x 1080
Number of Screens:	1
Product Family:	MP59G-P
Product Type:	LCD Monitor
Response Time:	5 ms
Screen Mode:	Full HD
Screen Size:	61 cm (24")
VGA:	Yes

General Information

Brand Name:	LG
Manufacturer Part Number:	24MP59G-P
Manufacturer Website Address:	http://www.lge.co.uk
Manufacturer:	LG Electronics
Product Model:	24MP59G-P
Product Name:	24" Class Full HD IPS Gaming Monitor (23.8" Diagonal) 24MP59G-P Black
Product Series:	MP59G-P
Product Type:	LCD Monitor

Interfaces/Ports

DisplayPort:	Yes
HDMI:	Yes
VGA:	Yes

Miscellaneous

Energy Star:	Yes
--------------	-----

Physical Characteristics

Colour:	Black
Depth with Stand:	203.20 mm
Depth:	86.4 mm
Height with Stand:	419.10 mm
Height:	332.7 mm
Weight (Approximate):	2.81 kg
Weight with Stand (Approximate):	3.22 kg
Width with Stand:	551.18 mm
Width:	551.2 mm

Power Description

Operating Power Consumption:	17.10 W
------------------------------	---------

Technical Information

Aspect Ratio:	16:9
Backlight Technology:	LED
Number of Screens:	1
Response Time:	5 ms
Screen Mode:	Full HD
Screen Size:	61 cm (24")

Video

Brightness:	250 cd/m ² 250 cd/m ²
Colour Support:	16.7 Million Colours
Contrast Ratio:	5,000,000:1
Maximum Resolution:	1920 x 1080
Tearing Prevention Technology:	FreeSync

Printed on: 11/12/2017 at 2:6:17

Prices and other details current at the time and date page was printed (subject to change).