


904-00965

Article Number: 904-00965

Description: Out of Rack Connectivity, 4U, Steel, Black, 1/box



Base Data	Local Order Number	ORC4U
	Type	ORC4U
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Maximizes cabling density outside of the cabinet/rack to reclaim data center floor space. • Universal mounting brackets provide simple, flexible mounting options for ladder rack or overhead cable tray. • Cable rings included for versatile cable routing and manageability for moves, adds or changes. • CEA-310-E compliant mounting holes for compatibility with data center hardware. • 12-gauge steel construction delivers 100-pound load rating.
	Quantity Per	box
	Product Description	<p>HellermannTyton's Out of Rack connectivity solution provides 4U of space to accommodate patch panels or additional active hardware above cabinets and racks without consuming additional floor space.</p> <p>It can be used as a Zone Distribution Area or Equipment Distribution Area for increased scalability. Standard 19" rack mount accepts traditional copper and fiber panels as well as RapidNet® pre-terminated solutions for swift deployment. Included universal mounting brackets provide flexibility to mount the rack in multiple positions on common ladder rack and overhead cable tray systems. This allows for improved cable routing between pathways and cabinets or racks.</p>
	GLOBAL PART NAME (auto set)	ORC4U-ST-BK
	Short Description	Out of Rack Connectivity, 4U, Steel, Black, 1/box
	Product Dimensions	
	Width W (Imperial)	19.0"
	Width W (Metric)	482.6mm
	Height H (Imperial)	8.39"
	Height H (Metric)	213.0mm
	Depth D (metric)	76.2mm
	Depth D (imperial)	3.0"

904-00965

Material and Specifications		
	Material	Steel (ST)
	Material Shortcut	ST
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1