

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2016060610](#)
Status: **Active**
Overview: High-Current, Universal-Clamp Terminal Blocks
Description: High Current Universal Clamp Terminal Block, 35.00mm DIN-rail Mount, 150.0A / 600V, Grey Housing and Cover, 1 Circuit

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E48521

General

Product Family Terminal Blocks
 Series [201606](#)
 Application Wire-to-Wire
 Component Type One Piece
 Overview [High-Current, Universal-Clamp Terminal Blocks](#)
 Product Literature Order No 987651-7108
 Product Name Universal Clamp
 Type Universal Clamp
 UPC 78172551120

Physical

Circuits (Loaded) 1
 Circuits (maximum) 1
 Color - Resin Grey
 Entry Angle Horizontal
 Lock to Mating Part None
 Material - Metal Aluminum
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Polyamide
 Number of Rows 1
 Orientation Vertical
 Panel Mount No
 Pitch - Mating Interface N/A
 Polarized to Mating Part N/A
 Stackable No
 Temperature Range - Operating -40°C to +105°C
 Termination Interface: Style Screw
 Wire Size AWG 1/0-6, 6+6, 8+8+8
 Wire Size mm² 13.00+13.00, 13.00-53.00, 8.30+8.30+8.30

Electrical


Current - Maximum per Contact 150.0A
 Voltage - Maximum 600V

Material Info

Engineering Number MX-KE61

Reference - Drawing Numbers

Sales Drawing 2016060610-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[201606 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION