

# PRO250 Inspection Light

## Rechargeable Led Inspection Lamp

**New**

Rechargeable and cordless the PRO250 uses a combination of new LED Technology strip for a powerful (250 lumens) light output and optical lens provides wide angle uniform illumination. Multi-positioning for directional lighting and magnet for hands free use. A high power LED torch mode and anti-slip comfortable grip. Li-ion battery for faster consistent recharging and reliability.



### Key features:

- Ultimate control over lighting direction - rotates 360° and 180° ratcheting
- Exceptional light output - new technology COB LED provides 250 lumens
- Produces clear white light
- Wide angle of light output that has uniform intensity.
- Magnet for hands free use
- Rechargeable and cordless
- Fast, consistent charging with lithium ion battery.
- Integrated hanging hook
- Resilient polycarbonate and ABS construction.
- Anti-slip comfortable grip
- Includes AC mains charge
- Drop proof up to 1m
- Runtime:
  - Flood 2.5hrs
  - Torch 6hrs

#### Supplied with:

- AC mains charger
- 12V + 24V DC vehicle charger
- Charging base
- Micro USB cable



PRODUCT CODE	DIMENSIONS
NSPRO250	(L)196X(W)80X(H)80mm

