


IRONMAN - Gauge Steel Closed Clip Shelving - Starter Kits

Quantum's IRONMAN Closed Shelving Units are ideal for industrial and commercial storage and organization. Closed shelving provides extra protection from dirt & dust, creates separation between areas and prevents product from falling off sides or back of unit. Units are available in 18 & 20 gauge, 4 heights and 15 shelf sizes. Each starter unit includes 4 offset posts (punched on 1" centers for easy adjustment), one back panel, 2 side panels and selected number of shelves with corresponding hardware (nuts and bolts for top and bottom shelves, clips for intermediate shelves). See shelf chart on pg. 94 for load weight capacity. Easy and quick assembly. Available in Gray.



4 SHELF STARTER KITS

EXTRA PROTECTION FROM DIRT & DUST, PREVENTS PRODUCT FROM FALLING OFF SIDES OR BACK OF UNIT



CL20G-75-1836-5

IRONMAN - Back and Side Panels

Offset back and side panels to be used with offset posts. Back and side panels are designed for extra protection against dirt & dust, creates separation between areas and provides a more orderly appearance. Back and side panels replace back and side sway braces. Order two side panels and one back panel per unit.

MODEL NO.	SHIP WGT
Side Panels	
SP-1239	4 lbs
SP-1539	5 lbs
SP-1839	6 lbs
SP-2439	9 lbs
SP-3039	10 lbs
SP-1275	8 lbs
SP-1575	10 lbs
SP-1875	12 lbs
SP-2475	18 lbs
SP-3075	20 lbs
SP-1287	12 lbs
SP-1587	15 lbs
SP-1887	18 lbs
SP-2487	27 lbs
SP-3087	30 lbs
SP-1299	12 lbs
SP-1599	15 lbs
SP-1899	18 lbs
SP-2499	27 lbs
SP-3099	30 lbs
Back Panels	
BP-3639	13 lbs
BP-4239	15 lbs
BP-4839	17 lbs
BP-3675	26 lbs
BP-4275	30 lbs
BP-4875	34 lbs
BP-3687	39 lbs
BP-4287	45 lbs
BP-4887	51 lbs
BP-3699	39 lbs
BP-4299	45 lbs
BP-4899	51 lbs

SHELF D" x W"	39"H			
	18 GAUGE		20 GAUGE	
MODEL NO.	SHIP WGT	MODEL NO.	SHIP WGT	
4 Shelf, 39"H Closed Shelving Unit				
12" x 36"	CL18G-39-1236-4 60 lbs	CL20G-39-1236-4 55 lbs		
15" x 36"	CL18G-39-1536-4 72 lbs	CL20G-39-1536-4 59 lbs		
18" x 36"	CL18G-39-1836-4 82 lbs	CL20G-39-1836-4 66 lbs		
24" x 36"	CL18G-39-2436-4 98 lbs	CL20G-39-2436-4 80 lbs		
30" x 36"	CL18G-39-3036-4 114 lbs	CL20G-39-3036-4 92 lbs		
12" x 42"	CL18G-39-1242-4 71 lbs	CL20G-39-1242-4 63 lbs		
15" x 42"	CL18G-39-1542-4 76 lbs	CL20G-39-1542-4 67 lbs		
18" x 42"	CL18G-39-1842-4 91 lbs	CL20G-39-1842-4 72 lbs		
24" x 42"	CL18G-39-2442-4 110 lbs	CL20G-39-2442-4 86 lbs		
30" x 42"	CL18G-39-3042-4 128 lbs	CL20G-39-3042-4 98 lbs		
12" x 48"	CL18G-39-1248-4 82 lbs	CL20G-39-1248-4 70 lbs		
15" x 48"	CL18G-39-1548-4 91 lbs	CL20G-39-1548-4 74 lbs		
18" x 48"	CL18G-39-1848-4 100 lbs	CL20G-39-1848-4 82 lbs		
24" x 48"	CL18G-39-2448-4 122 lbs	CL20G-39-2448-4 97 lbs		
30" x 48"	CL18G-39-3048-4 141 lbs	CL20G-39-3048-4 113 lbs		
5 Shelf, 39"H Closed Shelving Unit				
12" x 36"	CL18G-39-1236-5 68 lbs	CL20G-39-1236-5 62 lbs		
15" x 36"	CL18G-39-1536-5 83 lbs	CL20G-39-1536-5 66 lbs		
18" x 36"	CL18G-39-1836-5 94 lbs	CL20G-39-1836-5 74 lbs		
24" x 36"	CL18G-39-2436-5 114 lbs	CL20G-39-2436-5 91 lbs		
30" x 36"	CL18G-39-3036-5 133 lbs	CL20G-39-3036-5 106 lbs		
12" x 42"	CL18G-39-1242-5 81 lbs	CL20G-39-1242-5 71 lbs		
15" x 42"	CL18G-39-1542-5 86 lbs	CL20G-39-1542-5 75 lbs		
18" x 42"	CL18G-39-1842-5 105 lbs	CL20G-39-1842-5 82 lbs		
24" x 42"	CL18G-39-2442-5 128 lbs	CL20G-39-2442-5 97 lbs		
30" x 42"	CL18G-39-3042-5 150 lbs	CL20G-39-3042-5 112 lbs		
12" x 48"	CL18G-39-1248-5 94 lbs	CL20G-39-1248-5 79 lbs		
15" x 48"	CL18G-39-1548-5 105 lbs	CL20G-39-1548-5 84 lbs		
18" x 48"	CL18G-39-1848-5 116 lbs	CL20G-39-1848-5 93 lbs		
24" x 48"	CL18G-39-2448-5 147 lbs	CL20G-39-2448-5 111 lbs		
30" x 48"	CL18G-39-3048-5 166 lbs	CL20G-39-3048-5 131 lbs		
6 Shelf, 39"H Closed Shelving Unit				
12" x 36"	CL18G-39-1236-6 76 lbs	CL20G-39-1236-6 69 lbs		
15" x 36"	CL18G-39-1536-6 94 lbs	CL20G-39-1536-6 73 lbs		
18" x 36"	CL18G-39-1836-6 106 lbs	CL20G-39-1836-6 82 lbs		
24" x 36"	CL18G-39-2436-6 130 lbs	CL20G-39-2436-6 102 lbs		
30" x 36"	CL18G-39-3036-6 152 lbs	CL20G-39-3036-6 120 lbs		
12" x 42"	CL18G-39-1242-6 91 lbs	CL20G-39-1242-6 79 lbs		
15" x 42"	CL18G-39-1542-6 96 lbs	CL20G-39-1542-6 83 lbs		
18" x 42"	CL18G-39-1842-6 119 lbs	CL20G-39-1842-6 92 lbs		
24" x 42"	CL18G-39-2442-6 146 lbs	CL20G-39-2442-6 108 lbs		
30" x 42"	CL18G-39-3042-6 172 lbs	CL20G-39-3042-6 126 lbs		
12" x 48"	CL18G-39-1248-6 106 lbs	CL20G-39-1248-6 88 lbs		
15" x 48"	CL18G-39-1548-6 119 lbs	CL20G-39-1548-6 94 lbs		
18" x 48"	CL18G-39-1848-6 132 lbs	CL20G-39-1848-6 104 lbs		
24" x 48"	CL18G-39-2448-6 162 lbs	CL20G-39-2448-6 125 lbs		
30" x 48"	CL18G-39-3048-6 191 lbs	CL20G-39-3048-6 148 lbs		