

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Definite Purpose Contactor
Line Rated Current	40 A
Poles description	3P
Pole contact composition	3 NO
Range of product	DPA

Complementary

Motor power hp	3 hp 115 V AC 1 phase 10 hp 230 V AC 3 phases 7.5 hp 230 V AC 1 phase 20 hp 460 V AC 3 phases 25 hp 575 V AC 3 phases
Locked rotor rated current	200 A 460 V AC 160 A 575 V AC 240 A 277 V AC
System Voltage	600 V AC
[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Phase	3 phases
Electrical connection	Box lugs Quick connect terminals

Environment

Product certifications	CSA CE UL listed
------------------------	------------------------

Ordering and shipping details

Category	21344 - 8910 DPA 4_(40 AMP)
----------	-----------------------------

Discount Schedule	CP1B
GTIN	00785901073444
Nbr. of units in pkg.	1
Package weight(Lbs)	1.02
Returnability	Y
Country of origin	CN

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------