




KIT-8CH-HD-4DW-1

The Defender High Definition CCTV Kit
Comes Fully Loaded with 4 x 1080p Dome Cameras,
1000GB (Installed & Formatted) and
a Range of Accessories for an Instant Security Solution



- High Definition Preview, Recording and Playback
- Hybrid DVR with an Ergonomic, Easy Interface
- The Hybrid DVR Supports HD Recording in AHD, TVI, CVI, IP and CVBS Formats
- Simple, Seamless Set-Up with P2P Cloud Technology – Fully Network Compatible
- Remotely Access your Security System from Anywhere in the World Via our Free App and Software
- Robust Metal 1080p Cameras (IP66) with New & Improved SMD Technology giving Crystal Clear Infrared Imaging
- The Perfect Unit for Home, Retail, Office and Warehouse Applications
- Technical Support from a Friendly UK Based Team



System	Display Screen	Detailed OSD setup for customization
	Monitor Resolution	VGA and HDMI
	Encode Capability	8 x 1080, 8 x 720P (Analog HD); 4 x 1080 (Analog HD) and 4 x 960p (IP) Hybrid mode; 16 x 1080P, 16 x 960P, 16 x 720p, 4 x 5MP (IP)
Video	Motion Detection	Separate channel selection with selected video areas on multiple levels
	Recording Mode	Manual, Alarm, Automatic and Timed
	Local Playback	8 Channel Playback and Synchronization
	Video Search	Time, date, event and channel search
Record	Data Occupation	720P 20Gb/Day, 960H 12 - 20G/day per channel plus audio
	Video Storage	Local HDD/SSD or Network
	Backup Mode	Network Backup, USB portable HDD/SDD backup if required
	Video Input	4 Channel BNC
	Video Output	1 Channel VGA, 1 Channel HDMI
Interfaces	Audio Input	4 Channel
	Audio Output	1 Channel
	Alarm Input	n/a
	Alarm Output	n/a
	Network Port	Ethernet 10/100Mbps auto-sensing
	PTZ Control	Dependent of model of camera connected
	USB port	USB2.0 standard compatibility
	Power	Standard, regional compatible power input





Image Sensor	2MP CMOS Sensor
Resolution	1080P
Signal System	PAL / NTSC
Minimum Illumination	0.01Lux/F1.2
S/N Ratio	More than 45dB
Synchronous System	Internal
IR Distance	20 Meters
IR Power On	Photodiode AUTO Control
Video Output	CVBS / CVI / TVI / AHD
Power/Current	DC12V(+/-10%)/550mA
Lens	Board Lens 3.6mm
Weather Proof	Ip66
Dimension (mm)	Φ94.5 x 76(H)
Weight (g)	450
Operating Conditions	-10~+50°C RH95% MAX

Kit Contents:

- HD Hybrid 8 Channel with 1000GB HDD Installed & Formatted
- 4 x 1080P White Metal Dome with IR and OSD settings
- 4 x 18m BNC Shotgun Cable
- 1 x Power Splitter
- 1 x Power Supply
- 1 x Remote Control
- 1 x Mouse
- 1 x HDMI Cable
- 1 x Full Copper Patch Lead
- 1 x Manual
- Technical Support from a Friendly UK Based Team



Images shown are simulated,
for illustrative purposes