

P0:		Goodmans
	Product Photo	
General Feature	Customer Model No.(Brand)	G43227T2
	Panel(60Hz/120Hz/3D)	HV430FHB(60Hz)
	Destination Country	UK&EU
	Safety and Regulation	CE,ROHS
	Panel System	43 inch LED Panel(Approx. 109cm)
	Purpose	TV/Monitor Optional
	Aspect Ratio	16:9
	Max. Resolution	1920x1080
	Contrast Ratio (Typical)	4000:1(TYP) by panel
	Brightness(TYP cd/m2)	230nits(TYP) by panel
	Display Area(mm)	940.896 (H) x 59.254 (V)
	Pixel Pitch (mm)	0.4902(H) x 0.4902(W)
	Display Colors	16.7M
	Viewing Angle(L/R/U/D)	89/89/89/89(CR≥10)
	HD Supported Definitions	1080p/1080i/720P/576P/480P
	Response Time(Tr+Tf /typ.)	8ms
	AC Switch	N/A
	Cabinet Color	piano black
	Tilt Angle (up and down movement)	N/A
	Swivel Angle (left and right movement)	N/A
Wall Mounting Support(Screw Size)	VESA, 200 x 200mm(M5 x 10)	
Reception	TV Solution	Mstar3463
	TV System	ATV: PAL BG/DK/I SECAM BG/DK/L/L' DTV:DVB-T & DVB-C&DVB-T2, MPEG 2,MP@ML, MPEG 4
	TV Band	ATV 49MHz - 863MHz DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz)
	5V from Antenna	N/A
	NTSC Playback	N/A
	Digital Comb Filter	3D
	De-interlace Image Enhancement	N/A
	Tuning System	FST
	Clock / Time Display	N/A
	CI PLUS	N/A
Number of channel for storing	100 Analog / 400 Digital	
Sound	Bass	YES
	Treble	YES
	Balance	YES
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	2*8W
	Dolby	N/A
	SRS	N/A
Connectors Jack	RF Antenna	1
	HDMI	YESx3
	CVBS	YESx1
	PC In	D-sub 15Pin x 1
	Audio In	PC audio x 1(3.5 φ Mini Jack) CVBS Audio x1
	Scart	YESx 1
	YPbPr	YESx 1
	Digital Audio Out	YESx 1

	Earphone Out	YESx 1(3.5 φ Mini Jack)
	USB	YESx 1(Multi Media and PVR Movie: *.mpg, *.dat, *.vob, *.avi, *.ts, *.mov, *.mkv, *.mp4 Music: *.mp3, *.wma, *.m4a, *.aac Photo: *.jpg, *.bmp, *.png)
	CI	YESx 1
	RCA	N/A
Other Features	APS	ATV, DVBT, DVBC storage in capture order.
	OSD Language	English / French / German / Italian/Spanish/Portuguese
	Teletext	1000pages
	EPG (Electronic Program Guide)	7 days (not 7 days from satellite transmissions)
	Automatic Tuning	YES
	Sleep Timer	YES(240min)
	Noise Reduction	YES
	Color Temperature Adjustment	YES
	Picture Mode	Standard /Dynamkic/Mild /User
	Home Mode	YES
	Sleep Mode	YES
	Hotel Mode	YES
Power	Power Supply	AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	54W
	Max power Consumption	<120W
	Standby Power Consumption	0.4W
	Energy Efficiency Class	A+
Accessories	USER'S Manual	ENGLISH
	Remote Control	YESx 1
	Power Cable	YESx 1
	Adapter	N/A
	Adapter Cables	N/A
	Warranty	YES
	Battery	1.5V(AAA)×2
Dimension	Unit Dimension With Stand (W x H x D mm)	969*612*257mm
	Unit Dimension Without Stand (W x H x D mm)	969*564*86 mm
	Weight of unit(kg)	7.4Kg
	Weight of gift box with content(kg)	10.1
	Dimensions of mastercarton (W x H x D mm)	1072 x 173 x 654
	Weight of carton/paper(Kg)	/
	Weight of styrofoam(Kg)	/