



Toggle switches

9400.0201

Product number	9400.0201	
Business unit	Switches, Sensors & Controls	
Product family	Toggle switches	
Actuation type	direct	
Packing unit		100
Output	catalogue miniature switch	
Switching function	Changeover switch (DPDT)	
Material fixed contact	gold-plated	
Number of poles	2 - pole	
connections	PCB terminal, sealed	
Rating IEC	≤ 0.4V A 28 V	
Contact resistance (new condition)	< 80 mOhm	
Insulation resistance (new condition)	> 500 MOhm	
Voltage strength at 250 V	small contact distance	> 500 V
Protection type	Connection	washable
	Actuator	washable
Ambient temperature	-25 °C ... +70 °C	
Actuators and additional actuators	lever: thermosplastic glass fibre reinforced, gray	
Housing description	housing: thermoplastic glass fibre reinforced, black	
Connection surface	bearing connection	gold plated
	external connection	gold plated
Contact material	gold plated	
Contact type	slide contact	
Miscellaneous		
Type of fastening	pcb assembly	

Technical changes reserved. Dimensions are not binding.

Detailed specifications available on request.