

# WX 2021

2-Channel Soldering Station, 200 W (255 W)  
Code No.: T0053422699N



## Benefits


- › Power unit WX 2 with 2 channels, soldering irons WXMP and 1 tweezers WXMT
- › Simultaneous operation of 2 soldering stations




In addition we recommend:



Fume extraction devices



Soldering Irons



Cleaning Consumables



Preheating plates



Technical Data

Dimensions W x D x H (mm)	174 x 154 x 135
Dimensions W x D x H (Inch)	6,85 x 6,06 x 5,31
Weight (ca) in kg	3.45
Voltage	230 V, 50 Hz
Power output	200 W (255 W)
Channels	2
Temperature range (depends on tool) °C	100 - 550
Temperature range (depends on tool) °F	200 - 999
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding	Via 3,5 mm pawl socket on back of device
Display	255 x 128 dots / Backlighting
Air consumption l/min	---
Operating pressure	---
Capacity l/min	---
Vacuum	---

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE