

PNOZ m ES EtherNet/IP

772137



Configurable control system PNOZmulti 2 expansion module
Communication interface EtherNet/IP.

Technical details

Approvals:	CE;cULus Listed;CCC
Fieldbus interface:	EtherNet/IP
Fieldbus type:	Adapter
Transmission rate:	10 MBit/s;100 MBit/s
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	110.4 mm
Gross weight:	100 g
Net weight:	90 g
Ambient temperature:	0 - 60 °C

Accessories



783542

Spring terminals PNOZ mmcxp, 1 pc.



793542

Screw terminals PNOZ mmcxp, 1 pc.



793543

Screw terminals PNOZ mmcxp, 10 pcs.



783543

Spring terminals PNOZ mmcxp, 10 pcs.

Optional accessories



779260

PNOZ mm0.xp connector left (10 pcs)



793543

Screw terminals PNOZ mmcxp, 10 pcs.



783543

Spring terminals PNOZ mmcxp, 10 pcs.