

## PNOZ m ES ETH

772130



Configurable control system PNOZmulti 2 expansion module  
Communication interface Ethernet/Modbus-TCP interface.

### Technical details

Approvals:	CE;cULus Listed;CCC
Fieldbus interface:	Modbus/TCP
Fieldbus connection:	RJ45
Fieldbus type:	Slave
Number of Ethernet interfaces:	2
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	111.0 mm
Gross weight:	90 g
Net weight:	80 g
Ambient temperature:	0 - 60 °C

### Optional accessories



779260

PNOZ mm0.xp connector left (10 pcs)