

PNOZ m ES Profinet

772138



Configurable control system PNOZmulti 2 expansion module
Communication interface PROFINET.

Technical details

Approvals:	CE;cULus Listed
Fieldbus interface:	PROFINET
Transmission rate:	100 MBit/s
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	110.4 mm
Gross weight:	96 g
Net weight:	86 g
Ambient temperature:	0 - 60 °C

Accessories



783542

Spring terminals PNOZ mmcxp, 1 pc.



793542

Screw terminals PNOZ mmcxp, 1 pc.

Optional accessories



779260

PNOZ mm0.xp connector left (10 pcs)



793543

Screw terminals PNOZ mmcxp, 10 pcs.



783543

Spring terminals PNOZ mmcxp, 10 pcs.