

PNOZ m B1

772101



Configurable control system PNOZmulti 2 base module expandable, communication interface, 2 Ethernet interfaces, USB memory.

Technical details

Approvals:	CE;cULus Listed;TÜV;BG
Base unit:	Yes
Number of test pulse outputs:	4
Supply voltage (V):	24,0
Supply voltage type:	DC
Terminal type:	Cage clamp terminal;Screw terminal
Terminal style:	Plug-in
Version for extreme environ. conditions:	Standard
Width dimension:	45.0 mm
Height dimension:	120.2 mm
Depth dimension:	98.0 mm
Gross weight:	219 g
Net weight:	209 g
Ambient temperature:	0 - 60 °C

Optional accessories



751016

Set4 Spring Terminals



779213

USB Memory 512MB



750016

Set4 Screw Terminals