



60947-3

PICABOND® Connector, 1000 loose piece, 400 Vdc, red

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for butt, straight, bridge and half-tap splicing applications

Product Classification

Brand	PICABOND®
Product Series	PICABOND
Product Type	Splice
Regional Availability	Australia/New Zealand EMEA Latin America North America

Body Features

Cable Insulation Material	Air Core PIC Paper or Pulp
Color Code	Red
Sealant	Unfilled

Contact Features

Contact Base Material	Phosphor bronze
Contact Plating Material	Tin

Dimensions

Wire Size (CMA)	24 – 19 AWG
-----------------	-------------

Electrical Characteristics

Voltage Rating	400 Vdc
----------------	---------

Packaging Features

Packaging Method	Loose Piece
Packaging Quantity	1000

Product Type Features

Splicing Applications	Bridge Butt Full Bridge Half-tap Straight (In-line)
-----------------------	---

Usage Conditions

Operating Temperature	-40 – 60 °C
-----------------------	-------------

Regulatory Compliance/Certifications

Agency

Classification

Product Specifications

COMMSCOPE®

60947-3

RoHS 2011/65/EU

Compliant