

OMWS1PB



Products → Low Voltage Products and Systems → Switches → Cam Switches

General Information

Extended Product Type:	OMWS1PB
Product ID:	1SCA022532R6770
EAN:	4034656520915
Catalog Description:	OMWS1PB Cam switch
Long Description:	Black handle and frontplate with standard text are included. Special engraved frontplates to be ordered as separate items.

Additional Information

ABB Industrial IT Suite:	Control IT
Ampere Rating UL/CSA:	600 V AC 10 A
Color:	Black
Conventional Free-air Thermal Current (I_{th}):	q = 40 °C 10 A
Country of Origin:	Germany (DE)
Customs Tariff Number:	85365080
Data Sheet, Technical Information:	1SCC302003C0201
Declaration of Conformity - CE:	1SCC302001D0204
EAN:	4034656520915
ETIM 5:	EC002611 - Control switch
ETIM 6:	EC002611 - Control switch
Enclosure Type:	Not enclosed
Environmental Information:	1SCC302003D0201
Function:	WS1
Handle Type:	Basic handle
IT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SCC302004M0203
Invoice Description:	OMWS1PB Cam switch
Minimum Order Quantity:	1 piece
Mounting Type:	Snap-on door mounting
Number of Contacts:	2
Number of Poles:	1
Object Classification Code:	Q
Package Level 1 EAN:	4034656520915
Package Level 1 Gross Weight:	0.09 kg
Package Level 1 Height:	30 mm
Package Level 1 Length:	67 mm
Package Level 1 Units:	10 piece
Package Level 1 Width:	30 mm
Price Category:	Standard
Product Main Type:	OM
Product Name:	Cam switch
Product Net Depth:	67 mm
Product Net Height:	30 mm
Product Net Weight:	0.09 kg
Product Net Width:	30 mm
Rated Continuous Thermal Current:	FullyEnclosed 10 A
Rated Operational Voltage:	250 V
Replacement Product ID (NEW):	1SCA126517R1001
RoHS Information:	1SCC302004D0201
Selling Unit of Measure:	piece
Short Description:	Cam switch. Change-over switches. Miniature, door mounted
Special Functions:	Change-over switch: Without 0-position, step angle 60°, front plate 1-2
Terminal Type:	Screw Terminals

