

Products → Low Voltage Products and Systems → Enclosed Switches → Enclosed Cam Switches

## General Information

<b>Extended Product Type:</b>	ONA2EPB
<b>Product ID:</b>	1SCA022662R3410
<b>EAN:</b>	4034656523992
<b>Catalog Description:</b>	ONA2EPB Enclosed cam switch
<b>Long Description:</b>	Enclosed cam switch 2-p.400V AC23A AC22A 20A Plastic enclosure IP65 Black Selector handle

## Additional Information

<b>Ampere Rating UL/CSA:</b>	600 V AC 25 A
<b>Cable Entry Position:</b>	Up/Down
<b>Cable Outlets Per Side:</b>	M knock-outs
<b>Color:</b>	Black
<b>Conventional Free-air Thermal Current (<math>I_{th}</math>):</b>	q = 40 °C 25 A
<b>Conventional Thermal Current (<math>I_{the}</math>):</b>	Fully Enclosed 25 A
<b>Country of Origin:</b>	Germany (DE)
<b>Customs Tariff Number:</b>	85371099
<b>Data Sheet, Technical Information:</b>	1SCC302003C0201
<b>Declaration of Conformity - CE:</b>	1SCC302001D0204
<b>Degree of Protection:</b>	IP54 IP65
<b>E-nummer:</b>	3146265
<b>EAN:</b>	4034656523992
<b>ETIM 5:</b>	EC002611 - Control switch
<b>ETIM 6:</b>	EC002611 - Control switch
<b>Enclosure Material:</b>	Plastic
<b>Enclosure Type:</b>	Enclosed
<b>Environmental Information:</b>	1SCC302003D0201
<b>Function:</b>	A2
<b>Handle Type:</b>	Basic handle
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Industrial IT Certification Level:</b>	0
<b>Instructions and Manuals:</b>	1SCC302004M0203
<b>Invoice Description:</b>	ONA2EPB Enclosed cam switch
<b>Minimum Order Quantity:</b>	1 piece
<b>Mounting Type:</b>	Switch in enclosure
<b>Number of Contacts:</b>	2
<b>Number of Poles:</b>	2
<b>Object Classification Code:</b>	Q
<b>Order Multiple:</b>	1 piece
<b>Package Level 1 EAN:</b>	4034656523992
<b>Package Level 1 Gross Weight:</b>	0.4 kg
<b>Package Level 1 Height:</b>	120 mm
<b>Package Level 1 Length:</b>	157 mm
<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	132 mm

Storage Level (mm):	132 mm
Pollution Degree:	3
Price Category:	Standard
Product Main Type:	ON
Product Name:	Cam switch
Product Net Depth:	70 mm
Product Net Height:	96 mm
Product Net Weight:	0.3 kg
Product Net Width:	96 mm
Rated Continuous Thermal Current:	FullyEnclosed 25 A
Rated Impulse Withstand Voltage (U <sub>imp</sub> ):	4 kV
Rated Insulation Voltage (U <sub>i</sub> ):	690 V
Rated Operational Current AC-22A (I <sub>e</sub> ):	(500 V) 20 A (690 V) 20 A
Rated Operational Power AC-23A (P <sub>e</sub> ):	(220 ... 240 V) 2,6 kW
Rated Operational Voltage:	690 V
RoHS Information:	1SCC302004D0201
Selling Unit of Measure:	piece
Short Description:	Enclosed cam switch 2-p.400V AC23A AC22A 20A
Special Functions:	ON - OFF switch: 0-position: 9 o'clock, basic handle, step angle 90°, front plate 0-1
Terminal Type:	Screw Terminals

