

Products → Low Voltage Products and Systems → Enclosed Switches → Enclosed Cam Switches

General Information

Extended Product Type:	ONA4EPB
Product ID:	1SCA022662R3680
EAN:	4034656524012
Catalog Description:	ONA4EPB Enclosed cam switch
Long Description:	Enclosed cam switch 4-p.400V AC23A 7.5kW AC22A 20A Plastic enclosure IP65 Black Selector handle

Additional Information

Ampere Rating UL/CSA:	600 V AC 25 A
Cable Entry Position:	Up/Down
Cable Outlets Per Side:	M knock-outs
Color:	Black
Conventional Free-air Thermal Current (I_{th}):	q = 40 °C 25 A
Conventional Thermal Current (I_{the}):	Fully Enclosed 25 A
Country of Origin:	Germany (DE)
Customs Tariff Number:	85371099
Data Sheet, Technical Information:	1SCC302003C0201
Declaration of Conformity - CE:	1SCC302001D0204
Degree of Protection:	IP54 IP65
E-nummer:	3146267
EAN:	4034656524012
ETIM 5:	EC002611 - Control switch
ETIM 6:	EC002611 - Control switch
Enclosure Material:	Plastic
Enclosure Type:	Enclosed
Environmental Information:	1SCC302003D0201
Function:	A4
Handle Type:	Basic handle
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SCC302004M0203
Invoice Description:	ONA4EPB Enclosed cam switch
Minimum Order Quantity:	1 piece
Mounting Type:	Switch in enclosure
Number of Contacts:	4
Number of Poles:	4
Object Classification Code:	Q
Order Multiple:	1 piece
Package Level 1 EAN:	4034656524012
Package Level 1 Gross Weight:	0.4 kg
Package Level 1 Height:	120 mm
Package Level 1 Length:	157 mm
Package Level 1 Units:	1 piece
Package Level 1 Width:	132 mm

Storage Level (mm):	132 mm
Pollution Degree:	3
Price Category:	Standard
Product Main Type:	ON
Product Name:	Cam switch
Product Net Depth:	70 mm
Product Net Height:	96 mm
Product Net Weight:	0.3 kg
Product Net Width:	96 mm
Rated Continuous Thermal Current:	FullyEnclosed 25 A
Rated Impulse Withstand Voltage (U _{imp}):	4 kV
Rated Insulation Voltage (U _i):	690 V
Rated Operational Current AC-22A (I _e):	(500 V) 20 A (690 V) 20 A
Rated Operational Power AC-23A (P _e):	(220 ... 240 V) 2,6 kW (400 V) 7,5 kW (500 V) 4,8 kW (690 V) 4,8 kW
Rated Operational Voltage:	690 V
RoHS Information:	1SCC302004D0201
Selling Unit of Measure:	piece
Short Description:	Enclosed cam switch 4-p.400V AC23A 7.5kW AC22A 20A
Special Functions:	ON - OFF switch: 0-position: 9 o'clock, basic handle, step angle 90°, front plate 0-1
Terminal Type:	Screw Terminals

