

Digital Angle Measure


D03197

Digital Angle Measure/Protractor

FEATURES

Compact and portable device
 Clear and large digital LCD display
 Auto-rotate display
 Encompassing angle measurement range of 4 x 90°

Absolute/relative measurement conversion
 Degree and slope conversion
 Auto power off function
 Magnets in the base for a secure hold



- A Stainless steel sheet-Measuring faces, Securely attaches gauge to any metal surface.
- B LCD display - Large , easy to read digits.
- C ON/OFF BUTTON
- D 0% BUTTON - Degree/ percentage of slope conversion.
- E ABS/REL - Absolute/ relative measurement conversion.
- F HOLD BUTTON - Holding measured display values.
- G Battery compartment

SPECIFICATIONS

Range	4 x 90°
Resolution	0.1°
Dimensions	55 x 55 x 16mm
Operating temperature	0 °C~40 °C
Humidity	40-80%