

Plastic Digital Caliper


D03195

0-15mm/ 0-16" Digital Caliper

FEATURES

High precision digital readout on clear LCD display
Imperial or metric units at the touch of a button
Depth measuring blade

Step-measuring faces
For internal and external measurements
Low battery level indicator



SPECIFICATIONS

Range	0~150mm/ 6"
Resolution	0.1mm/ 0.01"
Repeatability	0.1mm/ 0.01"
Power	One 1.5 V cell battery <input type="checkbox"/>
	One CR2032 3 V battery <input checked="" type="checkbox"/>
Influence of humidity	Up to 80% non-condensing
Operating temperature	0 °C~40 °C
Storage temperature	-10 °C~60 °C

BATTERY REPLACEMENT

