



AURELIA® Robust Grip®

Examination Gloves



43897	(M)	ø 50	10 x 50
43898	(L)	ø 50	10 x 50
43899	(XL)	ø 50	10 x 50
43890	(XXL)	ø 50	10 x 50



Nitrile



Powder Free



Yellow



7.0 +/- 0.2 g



Diamond-Textured




5 Years

Premium quality Yellow Nitrile examination gloves with excellent diamond grip finish they offer greater tensile strength and protection than both Latex and Vinyl.

Nitrile examination gloves offer extra comfort and flexibility.

- 6mil Powder-Free Nitrile
- Non-Sterile
- Beaded cuff
- Ambidextrous
- Latex Free
- AQL 1.5

Sizes & Dimensions



M	95 ± 10 mm	min. 240 mm
L	110 ± 10 mm	min. 240 mm
XL	120 ± 10 mm	min. 240 mm
XXL	≥ 120 mm	min. 240 mm

Single wall thickness



- ① min. 0.20 mm
- ② min. 0.16 mm
- ③ min. 0.08 mm

Physical properties

	Unaged	Aged
Tensile Strength	min. 14.0 MPa	min. 14.0 MPa
Elongation	min. 500 %	min. 400 %
Strength at Break	min. 6N	min. 6N

Quality Signs & Certificates

89/686/EEC, 93/42/EWG

ISO 9001:2008, ISO 13485, CMDCAS 13485 (SGS)

EN 455 1-4

EN 420 : 2003 + A 1 : 2009

EN 374 2-3, EN 388

EN 1186: Food Contact Approved (SGS)

