

RHT1851R15 | 18V Cordless Hedge Trimmer, 50cm Blade (1x 1.5Ah)

Article: 5133002110



- High torque motor delivers powerful cutting performance for pruning hedges and shrubs.
- Excellent cutting quality through precision 50cm diamond-ground blades.
- Capable of cutting large branches with 22mm blade gap and sawing function.
- Anti-jam system prevents accidental blocking.
- Rotating rear handle with overmould for ease of use in multiple positions.
- HedgeSweep™ attachment offers easy removal of clippings.

	RHT1851R15
Article Number	5133002110
Battery pack capacity (Ah)	1.5
Battery type	Li-ion
Blade length [cm]	50
Blade speed (rpm)	2700
Blade type	Diamond ground
Charger included?	Yes
Charger supplied	60 min
Max. cutting capacity (mm)	18
No. of batteries supplied	1
Power	18V
Sound power level [dB(A)]	92
Sound power level guaranteed [dB(A)]	94
Sound power level uncertainty [dB(A)]	3
Sound pressure level (dB(A))	72
Sound pressure level uncertainty [dB(A)]	3
Stroke rate (spm)	18,500
Supplied in	Recyclable Carton
Vibration level [m/s ²]	<2.5
Vibration uncertainty [m/s ²]	1.5
Voltage (V)	18
Weight [without battery] [Kg]	1
Weight with battery pack (kg)	3.15