

R18DDP-0 | 18V Cordless Drill/Driver

Article: 5133002095



- Cordless Drill driver ideal for drilling in wood or metal and screw driving.
- Keyless chuck for quick and easy bit changes.
- 2 gears to control the max speed to match different materials and applications.
- 24 torque settings help to drive screws flush every time.
- For best performance and ergonomics we recommend using a 2.5Ah lithium+ battery which can drive up to 695 4x32mm screws per charge.

	R18DDP-0
Article Number	5133002095
Battery pack capacity (Ah)	-
Battery type	-
Charger included?	No
Charging time	-
Chuck capacity (mm)	13
Max drilling steel (mm)	13
Max. drilling wood (mm)	32
Max. torque (Nm)	45
No load speed (rpm)	0-440 / 0-1600
No. of batteries supplied	0
Power	18V
Sound power level measured [dB(A)]	90
Sound power level measured uncertainty [dB(A)]	3
Sound pressure level (dB(A))	79
Sound pressure level uncertainty [dB(A)]	3
Supplied in	Recyclable Carton
Torque settings	24
Vibration drilling into Metal [m/s ²]	1.8
Vibration drilling into metal uncertainty [m/s ²]	1.5
Vibration screw driving [m/s ²]	1.3
Vibration screw driving uncertainty [m/s ²]	1.5
Voltage (V)	18
Weight [without battery] [Kg]	1.4