

Product information

18V RANDOM ORBIT SANDER 5"



Satisfying the professional's needs

DBO180Z

Battery Type	Lithium-ion
Body only machine	1
Voltage	18 v
Speed Control	3 stage push button
Pad brake	1
Maximum Output	190 w
Orbits per Minute	7000/9500/11000 opm
Orbit Diameter	2.8 mm
Sanding Stroke per Minute	14000/19000/22000 spm
Paper Fastening	Hook & Loop
Pad Size	123 mm
Paper Size	125 mm
Vibration K factor	1.5 m/sec ²
Vibration: Sanding	2.5 m/sec ²
Net weight	1.7 kg



STANDARD EQUIPMENT: Dust bag

- Simple to operate electronic push button switch with 3-speed settings
- Fully Compatible with 18V 4.0Ah Battery with 36 minute charge time.
- Connectable to dust extractor
- Compact design with short height and lower centre of gravity for better manoeuvrability

Details correct as of: 9-1-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com