

# Product information

## 18V Combi Drill BL LXT



### DHP484RTJ

Capacity in Steel	13 mm
Capacity in Wood	38 mm
Chuck Capacity	1.5 - 13 mm
Capacity in Masonry	13 mm
Blows per Minute (Hi) - ipm	0 - 30,000 ipm
Blows per Minute (Lo) - ipm	0 - 7,500 ipm
No Load Speed (Hi)	0 - 2,000 rpm
No Load Speed (Lo)	0 - 500 rpm
Voltage	18 v
Torque Settings	21 + drill
Battery Type	Lithium-ion
Vibration K factor	1.5 m/sec <sup>2</sup>
Noise sound pressure	88 dB(A)
Noise sound power	99 dB(A)
Noise K factor	3 dB(A)
Net weight	1.8 kg
Battery Quantity (5.0ah)	2
Max. Fastening Torque (Soft Joint)	30 Nm
Max. Fastening Torque (Hard Joint)	54 Nm
Vibration: Impact drilling into concrete	8.0 m/sec <sup>2</sup>
Vibration: Drilling into metal	2.5 m/sec <sup>2</sup>



LITHIUM-ION

BL  
MOTOR

**STANDARD EQUIPMENT:** 197282-4 Battery BL1850B 18v Li-ion, 821550-0 MAKPAC CONNECTOR CASE (TYPE 2), 837916-4 MAKPAC INLAY FOT TYPE 2 CASE, DC18RC DC18RC COMPACT CHARGER

- Brushless motor
- Electric brake
- 2 mechanical gears.
- Variable speed control by trigger
- Forward/reverse rotation
- LED job light
- Compact Overall Length of 182mm
- Keyless Chuck
- Aluminium Gear Housing
- All metal gear construction
- Ergonomic soft grip
- Belt clip

Details correct as of: 9-1-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makita.com](http://www.makita.com)