


KEMET, MPLCV, Power, 47 uH, 20%



Dimensions	
Chip Size	3126
L	7.9mm MAX
W	6.7mm +/-0.4mm
T	5.4mm MAX

Packaging Specifications	
Packaging:	T&R, 380mm
Packaging Quantity:	1000

General Information	
Series:	MPLCV
Style:	SMD Chip
Description:	Surface Mount Inductor
Features:	Power Inductors, Automotive
RoHS:	Yes
Core:	Composite
Miscellaneous:	40 (K) Temperature Rise Max.

Specifications	
Inductance:	47 uH (0.1 MHz)
Inductance Tolerance:	20%
Temperature Range:	-20/+150C
Shielded:	Yes
Current:	3 A (Isat, 30% Drop In Inductance), 2.1 A (Irms, 40C Rise By Self Heating)