



## J.S.T. (U.K.) LTD. CRIMP SPECIFICATIONS

<b>TERMINAL PART NUMBER</b>	SPAL-001T-P0.5
<b>STRIP LENGTH (MM)</b>	2.5 mm

APPLICABLE WIRE SIZE	CONDUCTOR BARREL		INSULATION BARREL		TENSILE (NEWTONS)
	HEIGHT	WIDTH	HEIGHT	WIDTH	
0.3 mm <sup>2</sup>	0.65-0.70	1.40	*	1.40	40N
26 AWG	0.60-0.70	1.40	*	1.40	20N
24 AWG	0.65-0.75	1.40	*	1.40	30N
22 AWG	0.70-0.80	1.40	*	1.40	40N

### COMMENTS:

\* INSULATION CRIMP HEIGHT IS DEPENDANT ON THE SPECIFICATION OF THE WIRE USED.

CRIMP HEIGHTS SPECIFIED ARE FOR GUIDANCE ONLY AND MAY VARY DEPENDING ON THE WIRE CONSTRUCTION AND TOLERANCE.

### GENERAL TOLERANCE:

CONDUCTOR HEIGHT - N/A  
CONDUCTOR WIDTH - +/- 0.05  
INSULATION HEIGHT - N/A  
INSULATION WIDTH - +/- 0.10

FOR SPECIFIC WIRES PLEASE CONTACT J.S.T. (U.K.) LTD.

Prepared by:	Approved by:
PDS	MS
12-05-04	12-05-04