



Sample photo

Order symbol: ALN 060605
Product nbr: 7811060
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016034
EI. number:
 Finland: 3413045
 Electric No. 8212045619
 Denmark:
 Electric No. Sweden: 2536305

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions: Length Width Height **Accessories:**

mm:	66	60	46	MIV 5	DIN-35 Mounting rail
inch:	2.6	2.4	1.8	MR 75003	Selftapping taptite screw M3
				MRS 28540	Wall fastening lug (2 pcs)

Materials: **Rating:**

Material: Aluminium	Ingress Protection (EN 60529): IP66/IP67/IP68
Base colour: RAL 7001	Impact Resistance (EN 62262): IK08
Cover screws material: Stainless steel	NEMA Class: NEMA 1, 4, 4X, 12, 13
Cover colour: RAL 7001	
Gasket material: Polyurethane	

Certificates:

SGS Fimko

Temperatures:

Temperature °C (short term):	-50 ... 140 °C
Temperature °C (continuous):	-50 ... 80 °C
Temperature °F (short term):	-60 ... 285 °F
Temperature °F (continuous):	-60 ... 175 °F

Accessories:

TRM 0507	DIN-15 Mounting rail
----------	----------------------

